

Garant GRIDLINE

Energy casing with hose reel, Height: 600mm**Order data**

Order number	927328 600
GTIN	4062406108588
Item class	9GG

Description**Version:**

16G cabinet casing in sturdy steel construction.

Equipped with 2 × No. 928470 size DE250V/1, cable reel / hose reel, securely bolted to the casing base. Length on the cable reel 10 m. Length on the hose reel 10 m.

Connection NW 7.2 male coupling and quick-release coupling. With quick-lock coupling. Max. pressure 12 bar.

Fitted with:

Module No. 928470: 2 × size DE250V/1; 1 × size 0/1

Colour:

Body and modules RAL 7035 light grey, front RAL 7016 anthracite **powder-coated**.

Note:

Further individual configuration options with modules No. 928470. Keep within the maximum permissible number of modules.

Technical description

Height	600 mm
Weight	25.4 kg

Depth	650 mm
Width	400 mm
Power supply	Mains operated
Nominal voltage	250 V
Plug type, input	GST plug-in system
Number of sockets type F	2
Socket type	F
Material thickness	1 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Power module

Accessories

Module for energy and media Module type 0/1	928470 0/1
Module for energy and media Module type DE250V/1	928470 DE250V/1