

Garant GRIDLINE

16G cabinet casing with power and compressed air modules, Height: 800mm**Order data**

Order number	927325 800
GTIN	4062406108526
Item class	9GG

Description**Version:**

16G cabinet casing in sturdy steel construction.

Equipped with power and compressed air modules: 2 × module No. 928470 size DE250V/1, 1 × module No. 928470 size AIR/S.

Fitted with:

Modules No. 928470: 2 pcs. size DE250V/1; 1 pc. size AIR/S; 1 pc. size 0/3

Colour:

Body and modules in RAL 7035 light grey. Front in RAL 7016 anthracite, **powder coated**.

Note:

Further individual configuration options with modules No. 928470. Keep within the maximum permissible number of modules.

Technical description

Depth	650 mm
Weight	25.2 kg
Width	400 mm
Height	800 mm

Power supply	Mains operated
Number of sockets type F	2
Plug type, input	GST plug-in system
Nominal voltage	250 V
Socket type	F
Material thickness	1 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Power module

Accessories

Module for energy and media Module type 0/1	928470 0/1
Module for energy and media Module type AIR/S	928470 AIR/S
Module for energy and media Module type 0/2	928470 0/2
Module for energy and media Module type DE250V/1	928470 DE250V/1
Module Module type AIR/S	933913 AIR/S