

**Abrasive sleeve, conical (ZA), 80 grit medium, largest sleeve Ø× sleeve width: 20X63mm****Order data**

Order number	553873 20X63
GTIN	4045197723314
Item class	52E

Description**Version:**

Made of non-tearing, synthetic resin bonded material with long service life and good grit adhesion.

Zirconium Aluminium Oxide (ZA).

The rubber body of the abrasive sleeve holder expands at high speed to hold the abrasive sleeve in place. The full width of the sleeve can be used, it does not slip and can be replaced quickly and easily (twist in the direction of slots when fitting/removing). Only compatible with abrasive sleeve holders.

Application:

Abrasive sleeves are predominantly used for surface grinding tasks which require the removal of large amounts of material – even at sharp edges.

Suitable for:

Abrasive sleeve holder No. 553830.

Technical description

Sleeve width	63 mm
largest sleeve Ø	20 mm
Grit	80
Grit designation	medium
Grinding media	Zirconium aluminium oxide

Grinding medium code	ZA
Sleeve shape	conical
Type of product	Abrasive sleeve

User data

	Suitability	V _c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
Wood	suitable only under restricted conditions		
dry	suitable		

Accessories

Abrasive sleeve holder slit, conical shank 6 mm Ø largest
Ø×head length 20X63 mm

553830 20X63