


eco grooving toolholder, Blade height h_5 / Shank height h : 26/25 mm

Order data

Order number	273868 26/25
GTIN	4045197722935
Item class	21W

Description
Note:

Coolant transfer only in conjunction with GARANT eco-system toolholders No. 319001 – 319886.

Through-coolant: true

Clamping claw: 279991

Clamping screw: 279990

Blade height h_5 : 26 mm

h_4 : 25 mm

h_2 : 6 mm

h_3 : 49 mm

b : 25 mm

b_3 : 48 mm

Technical description

h_4	25 mm
h_2	6 mm
Shank height h	25 mm
Shoulder length b	25 mm
h_3	49 mm

Shank width b_3	48 mm
Overall length L_{tot}	90 mm
Through-coolant	yes
Clamping claw	279840 2
Clamping screw	279815 14

Accessories

Clamping screw	279990
Clamping claw	279991
Torx® bit, shank E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cN·m	659906 500