



eco grooving toolholder, Blade height h₅ / Shank height h: 32/20 mm



Order data

Order number	273868 32/20
GTIN	4045197722966
Item class	21W

Description

Note:

Coolant transfer only in conjunction with GARANT eco-system toolholders No. 319001 – 319886.

Through-coolant: true

Clamping claw: 279991

Clamping screw: 279990

Blade height h₅: 32 mm

h₄: 20 mm

h₂: 14.1 mm

h₃: 54.5 mm

b: 20 mm

b₃: 43 mm

Technical description

Shank height h	20 mm
h ₃	54.5 mm
h ₂	14.1 mm
h ₄	20 mm
Shoulder length b	20 mm

Shank width b_3	43 mm
Overall length L_{tot}	78 mm
Through-coolant	yes
Clamping claw	279840 2
Clamping screw	279815 14

Accessories

Clamping claw	279991
Clamping screw	279990
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cN·m	659906 500
Torx® bit, shank E 6.3 Torx® profile TX15	674248 TX15