



ER collet chuck Form AD, SK 40 A = 100, for ER collet size: 25



Order data

Order number	300505 25
GTIN	4062406108700
Item class	32A

Description

Version:

Taper ground internally and externally. With Balluff/RFID chip bore.

HOLEX –

HOLEX precision clamping nut, balanced (G6.3 / 18,000 rpm, all shanks fine bead blasted. Balancing quality G6.3 / 18,000 rpm).

Application:

For clamping tools with plain shank in collets to DIN 6499 – Form A and B.

Supplied with:

Clamping nut.

Optional extras:

Pull studs (PS) No. 308600 – 308806, PS pull stud wrenches No.308820 – 308835, ER chuck key No. 309680 – 613300, ER collets No. 308901 – 309449, ER clamping nuts No. 309615 (for sealing rings), sealing rings No. 309625 – 309645 (for No. 309615).

Machining strategy: HSC

Clamping range: 1 - 16 mm

Overhang dimension A: 100 mm

External Ø D: 42 mm

Spare GARANT high-speed clamping nut No. 309610: 25

Spare HOLEX nut No. 309580: 25

Technical description

Overhang dimension A	100 mm
----------------------	--------

External Ø D	42 mm
Spare HOLEX nut No. 309580	25
Spare GARANT high-speed clamping nut No. 309610	25
Clamping range	1 - 16 mm
Clamping Ø D ₁	1-16 mm
Adapter	SK 40 A = 100
Arbor standard	ISO 7388-1
Shape	AD
Balance quality G at rotational speed	G 6.3 at 18,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HSC
Balluffchip bore	yes
Type of product	Collet chuck

Accessories

ER clamping nut for HiRunER collet chucks for ER 25	309617 25
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 10 mm	309413 10
ER collet for machine taps with seal Nominal clamping Ø d 4,5 mm	309411 4,5
ER collet HP with seal and spray nozzles Nominal clamping Ø d 14 mm	309375 14
Wrench for pull studs DIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 8 mm	309447 8
ER collet Nominal clamping Ø d 5 mm	308960 5
ER collet HP Nominal clamping Ø d 10 mm	309373 10
Pull stud Mazak, form A suitable for steep tapers 40M	308670 40M

ER collet Nominal clamping Ø d 6 mm	308960 6
ER collet for machine taps with seal Nominal clamping Ø d 9 mm	309411 9
ER collet HP Nominal clamping Ø d 2 mm	309373 2
ER collet for machine taps with seal Nominal clamping Ø d 4,5 mm	309409 4,5
ER collet with seal Nominal clamping Ø d 14 mm	308946 14
ER chuck key for ER collet chuck 25	309680 25
ER clamping nut High Speed for ER 25	309610 25
ER collet HP Nominal clamping Ø d 13 mm	309373 13
ER collet set HP with seal (4; 6; 8; 10; 12; 14; 16mm) 429 E	309394
Pull stud, 18CrNiMo7 sealed, form B suitable for steep tapers 40	308615 40
ER collet with seal Nominal clamping Ø d 5 mm	308959 5
Hurco 45° pull stud with 4-mm bore and fit sealed suitable for steep tapers 40	308801 40
ER collet HP Nominal clamping Ø d 6 mm	309373 6
ER collet for machine taps with seal Nominal clamping Ø d 16 mm	309411 16
ER collet Nominal clamping Ø d 6 mm	308941 6
ER collet set 7 pieces 4–16 mm with seal	309022
ER collet Nominal clamping Ø d 3 mm	308941 3
Torque wrench with reversible ratchet maximum torque 200 N·m	656050 200
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 7 mm	309447 7
Torque insert for ER Mini nuts for ER collet chuck 25	309745 25
ER collet with seal and spray nozzles Nominal clamping Ø d 5 mm	308962 5
Special pull stud with no internal thread sealed suitable for steep tapers 40	308700 40
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 8 mm	309413 8

ER collet Nominal clamping \varnothing d 14 mm	308941 14
Special pull stud with no internal thread sealed suitable for steep tapers 40	308720 40
ER collet for machine taps with seal and spray nozzles Nominal clamping \varnothing d 11 mm	309413 11
ER collet for machine taps with seal and spray nozzles Nominal clamping \varnothing d 7 mm	309413 7
Pull stud Hurco 90° with fit sealed suitable for steep tapers 40	308806 40
ER collet for machine taps with seal Nominal clamping \varnothing d 11 mm	309409 11
ET collet with radial compensation for tapping and reaming Nominal clamping \varnothing d 10 mm	309447 10
ER collet with seal and spray nozzles Nominal clamping \varnothing d 13 mm	308962 13
ER collet Nominal clamping \varnothing d 5 mm	308941 5
ER collet for machine taps with seal and spray nozzles Nominal clamping \varnothing d 9 mm	309413 9
ER collet HP with seal and spray nozzles Nominal clamping \varnothing d 4 mm	309375 4
ER collet Nominal clamping \varnothing d 2 mm	308941 2
ER collet with seal and spray nozzles Nominal clamping \varnothing d 10 mm	308962 10
ER collet with seal and spray nozzles Nominal clamping \varnothing d 8 mm	308962 8
ER collet Nominal clamping \varnothing d 8 mm	308960 8
ER collet with seal Nominal clamping \varnothing d 10 mm	308959 10
ER collet Nominal clamping \varnothing d 9 mm	308960 9
ER collet Nominal clamping \varnothing d 8 mm	308941 8
ET collet for thread tapping, with axial compensation Nominal clamping \varnothing d 7 mm	309430 7
ER collet with seal Nominal clamping \varnothing d 15 mm	308946 15
ER collet for machine taps with seal Nominal clamping \varnothing d 6 mm	309411 6

ER collet with seal Nominal clamping Ø d 11 mm	308959 11
ER collet HP with seal Nominal clamping Ø d 8 mm	309374 8
ER collet HP Nominal clamping Ø d 5 mm	309373 5
ER collet HP with seal Nominal clamping Ø d 10 mm	309374 10
ER collet HP with seal and spray nozzles Nominal clamping Ø d 6 mm	309375 6
ER collet Nominal clamping Ø d 12 mm	308960 12
ER collet with seal Nominal clamping Ø d 9 mm	308959 9
ER collet for machine taps with seal Nominal clamping Ø d 7 mm	309409 7
ER collet with seal Nominal clamping Ø d 12 mm	308959 12
ER collet Nominal clamping Ø d 2 mm	308960 2
ER collet with seal Nominal clamping Ø d 4 mm	308959 4
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 3,5 mm	309430 3,5
ER collet HP Nominal clamping Ø d 3 mm	309373 3
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 10 mm	309430 10
ER collet Nominal clamping Ø d 15 mm	308960 15
Pull stud 45° sealed suitable for steep tapers 40	308765 40
ER collet with seal and spray nozzles Nominal clamping Ø d 7 mm	308962 7
ER collet Nominal clamping Ø d 9 mm	308941 9
ER collet with seal Nominal clamping Ø d 8 mm	308946 8
Pull stud Mori-Seiki, sealed, form A suitable for steep tapers 40	308630 40
ER collet HP with seal and spray nozzles Nominal clamping Ø d 10 mm	309375 10
ER collet with seal Nominal clamping Ø d 7 mm	308959 7
ER collet Nominal clamping Ø d 13 mm	308960 13
ER collet with seal Nominal clamping Ø d 14 mm	308959 14
ER collet with seal Nominal clamping Ø d 4 mm	308946 4

ER plain bearing clamping nut for ER 25	309612 25
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 9 mm	309447 9
ER collet HP Nominal clamping Ø d 4 mm	309373 4
ER collet with seal Nominal clamping Ø d 6 mm	308959 6
ER collet with seal Nominal clamping Ø d 8 mm	308959 8
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 2,8 mm	309430 2,8
Special pull stud with internal thread suitable for steep tapers 40	308740 40
ER collet Nominal clamping Ø d 4 mm	308941 4
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 4,5 mm	309413 4,5
Pull stud 90° sealed suitable for steep tapers 40	308795 40
Pull stud 90° sealed suitable for steep tapers 40	308790 40
Pull stud sealed suitable for steep tapers 40	308660 40
ER collet with seal Nominal clamping Ø d 16 mm	308959 16
ER collet with seal and spray nozzles Nominal clamping Ø d 6 mm	308962 6
ER collet Nominal clamping Ø d 7 mm	308960 7
Wrench for pull studs ISO 7388 suitable for ISO taper size 40	308830 40
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 6 mm	309430 6
ER collet for machine taps with seal Nominal clamping Ø d 8 mm	309409 8
ER collet with seal Nominal clamping Ø d 9 mm	308946 9
Torque insert for Pull studs to DIN 69872 suitable for ISO taper size 40	308810 40
ER collet for machine taps with seal Nominal clamping Ø d 7 mm	309411 7
ER collet Nominal clamping Ø d 13 mm	308941 13
	309447 3

ET collet with radial compensation for tapping and reaming Nominal clamping \varnothing d 3 mm	
ER collet for machine taps with seal Nominal clamping \varnothing d 12 mm	309409 12
ER collet HP with seal Nominal clamping \varnothing d 15 mm	309374 15
ER collet for machine taps with seal Nominal clamping \varnothing d 6 mm	309409 6
ER collet for machine taps with seal Nominal clamping \varnothing d 14 mm	309411 14
ER collet with seal Nominal clamping \varnothing d 11 mm	308946 11
ER collet with seal and spray nozzles Nominal clamping \varnothing d 3 mm	308962 3
ER collet with seal Nominal clamping \varnothing d 3 mm	308946 3
ER collet with seal and spray nozzles Nominal clamping \varnothing d 4 mm	308962 4
ER collet with seal Nominal clamping \varnothing d 16 mm	308946 16
ER collet HP Nominal clamping \varnothing d 9 mm	309373 9
ER collet for machine taps with seal Nominal clamping \varnothing d 12 mm	309411 12
Pull stud Form B suitable for steep tapers 40	308640 40
ER collet with seal and spray nozzles Nominal clamping \varnothing d 11 mm	308962 11
ER collet with seal and spray nozzles Nominal clamping \varnothing d 9 mm	308962 9
Pull stud Mori-Seiki, sealed, form A suitable for steep tapers 40	308625 40
ER collet set 15 pieces 2–16 mm	309240
ER collet HP Nominal clamping \varnothing d 8 mm	309373 8
ET collet with radial compensation for tapping and reaming Nominal clamping \varnothing d 5 mm	309447 5
ER collet set 15 pieces 2–16 mm with seal	309244
ER collet HP with seal Nominal clamping \varnothing d 11 mm	309374 11
ER collet Nominal clamping \varnothing d 10 mm	308941 10

ER collet Nominal clamping Ø d 2,5 mm	308941 2,5
ER collet HP Nominal clamping Ø d 14 mm	309373 14
ER collet HP with seal and spray nozzles Nominal clamping Ø d 8 mm	309375 8
ER collet with seal Nominal clamping Ø d 15 mm	308959 15
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 4,5 mm	309447 4,5
ER collet HP with seal Nominal clamping Ø d 14 mm	309374 14
ER collet with seal Nominal clamping Ø d 7 mm	308946 7
Pull stud sealed, form B suitable for steep tapers 40	308650 40
ER collet Nominal clamping Ø d 15 mm	308941 15
ER collet HP with seal and spray nozzles Nominal clamping Ø d 12 mm	309375 12
ER collet for machine taps with seal Nominal clamping Ø d 14 mm	309409 14
ER collet HP with seal Nominal clamping Ø d 9 mm	309374 9
ER collet HP Nominal clamping Ø d 11 mm	309373 11
ER collet Nominal clamping Ø d 14 mm	308960 14
ER collet with seal Nominal clamping Ø d 6 mm	308946 6
ER collet Nominal clamping Ø d 3 mm	308960 3
ER collet for machine taps with seal Nominal clamping Ø d 11 mm	309411 11
Pull stud 60° sealed suitable for steep tapers 40	308785 40
ER clamping nut for ER 25	309580 25
ER collet with seal and spray nozzles Nominal clamping Ø d 15 mm	308962 15
Torque insert for Pull studs to SO 7388 suitable for ISO taper size 40	308812 40
ER collet with seal Nominal clamping Ø d 13 mm	308959 13
ER collet Nominal clamping Ø d 7 mm	308941 7
ER collet HP with seal Nominal clamping Ø d 7 mm	309374 7
	309413 6

ER collet for machine taps with seal and spray nozzles
Nominal clamping Ø d 6 mm

Pull stud 45° sealed suitable for steep tapers 40	308760 40
ER collet for machine taps with seal Nominal clamping Ø d 9 mm	309409 9
ER collet Nominal clamping Ø d 16 mm	308960 16
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 3,5 mm	309447 3,5
ER collet HP Nominal clamping Ø d 7 mm	309373 7
ER collet for machine taps with seal Nominal clamping Ø d 10 mm	309409 10
Pull stud, 18CrNiMo7 Form A suitable for steep tapers 40	308605 40
ER collet with seal and spray nozzles Nominal clamping Ø d 12 mm	308962 12
ER collet HP with seal Nominal clamping Ø d 13 mm	309374 13
ER collet set 15 pieces 2–16 mm with seal and spray nozzles	309245
ER collet with seal Nominal clamping Ø d 3 mm	308959 3
ER collet HP Nominal clamping Ø d 15 mm	309373 15
Pull stud Hurco 45° with fit sealed suitable for steep tapers 40	308802 40
ER collet with seal Nominal clamping Ø d 5 mm	308946 5
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 9 mm	309430 9
ER collet Nominal clamping Ø d 10 mm	308960 10
ER collet for machine taps with seal Nominal clamping Ø d 16 mm	309409 16
ER collet HP with seal Nominal clamping Ø d 3 mm	309374 3
ER collet HP Nominal clamping Ø d 16 mm	309373 16
ER collet HP with seal Nominal clamping Ø d 4 mm	309374 4
ER collet Nominal clamping Ø d 11 mm	308941 11
Pull stud sealed, form B suitable for steep tapers 40	308620 40

ER collet Nominal clamping Ø d 11 mm	308960 11
Pull stud sealed suitable for steep tapers 40	308635 40
ER collet with seal Nominal clamping Ø d 10 mm	308946 10
Pull stud sealed, form A suitable for steep tapers 40	308610 40
ER collet Nominal clamping Ø d 4 mm	308960 4
ER collet HP with seal Nominal clamping Ø d 5 mm	309374 5
ER collet HP with seal Nominal clamping Ø d 16 mm	309374 16
ER collet with seal and spray nozzles Nominal clamping Ø d 16 mm	308962 16
ER collet Nominal clamping Ø d 12 mm	308941 12
ER collet with seal and spray nozzles Nominal clamping Ø d 14 mm	308962 14
ER collet with seal Nominal clamping Ø d 12 mm	308946 12
ER collet Nominal clamping Ø d 16 mm	308941 16
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 8 mm	309430 8
ER collet with seal Nominal clamping Ø d 13 mm	308946 13
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 4,5 mm	309430 4,5
ER collet HP with seal Nominal clamping Ø d 6 mm	309374 6
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 12 mm	309413 12
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 6 mm	309447 6
ER collet for machine taps with seal Nominal clamping Ø d 10 mm	309411 10
ER collet HP with seal Nominal clamping Ø d 12 mm	309374 12
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 14 mm	309413 14
ER collet for machine taps with seal Nominal clamping Ø d 8 mm	309411 8
ER collet HP Nominal clamping Ø d 12 mm	309373 12

ET collet with radial compensation for tapping and reaming Nominal clamping \varnothing d 4 mm

309447 4