



## Reducing adapter SK / MT for tangs, form AD, BT 40, MT internal: 2



### Order data

Order number	303082 2
GTIN	4062406109226
Item class	32A

### Description

**Version:**

Ground internally and externally.

**Application:**

For clamping tools **with MT shank.**

**Optional extras:**

Pull studs (PS) No. 308760 – 308806.

Concentricity:  $\leq 8 \mu\text{m}$

Overhang dimension A: 50 mm

External  $\varnothing$  D: 32 mm

### Technical description

External $\varnothing$ D	32 mm
Overhang dimension A	50 mm
Adapter	BT 40
Standard	DIN 6383
Arbor standard	JIS B6339
Arbor standard	ISO 7388-2
Shape	AD

Balance quality G at rotational speed	G 6.3 at 15,000 rpm
Concentricity	≤ 8 μm
Type of product	Arbor adapter

## Accessories

Wrench for pull studs DIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
Pull stud 45° sealed suitable for steep tapers 40	308765 40
Torque insert for Pull studs to SO 7388 suitable for ISO taper size 40	308812 40
Torque insert for Pull studs to DIN 69872 suitable for ISO taper size 40	308810 40
Pull stud 90° sealed suitable for steep tapers 40	308795 40
Pull-stud 60° sealed suitable for steep tapers 40	308780 40
Pull stud Hurco 45° with fit sealed suitable for steep tapers 40	308802 40
Pull stud Hurco 60° with fit sealed suitable for steep tapers 40	308804 40
Pull stud 45° sealed suitable for steep tapers 40	308760 40
Wrench for pull studs ISO 7388 suitable for ISO taper size 40	308830 40
Hurco 60° pull stud with bore and fit sealed suitable for steep tapers 40	308803 40
Pull stud 60° sealed suitable for steep tapers 40	308785 40
Pull stud 90° sealed suitable for steep tapers 40	308790 40
Pull stud Hurco 90° with bore and fit sealed suitable for steep tapers 40	308805 40
Pull stud Hurco 45° with bore and fit sealed suitable for steep tapers 40	308801 40
Pull stud Hurco 90° with fit sealed suitable for steep tapers 40	308806 40

