



Reducing adapter SK / MT for tangs, form AD, BT 50, MT internal: 2



Order data

Order number	303087 2
GTIN	4062406109264
Item class	32A

Description

Version:

Ground internally and externally.

Application:

For clamping tools **with MT shank.**

Optional extras:

Pull studs (PS) No. 308760 – 308806.

Concentricity: $\leq 8 \mu\text{m}$

Overhang dimension A: 60 mm

External \varnothing D: 32 mm

Technical description

External \varnothing D	32 mm
Overhang dimension A	60 mm
Adapter	BT 50
Standard	DIN 6383
Arbor standard	ISO 7388-2
Arbor standard	JIS B6339
Shape	AD

Balance quality G at rotational speed	G 6.3 at 15,000 rpm
Concentricity	≤ 8 μm
Type of product	Arbor adapter

Accessories

Pull stud 45° sealed suitable for steep tapers 50	308765 50
Pull stud 45° sealed suitable for steep tapers 50	308760 50
Torque insert for Pull studs to DIN 69872 suitable for ISO taper size 50	308810 50
Pull-stud 60° sealed suitable for steep tapers 50	308780 50
Pull stud 90° sealed suitable for steep tapers 50	308790 50
Wrench for pull studs DIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 50	308820 50
Pull stud 60° sealed suitable for steep tapers 50	308785 50
Wrench for pull studs ISO 7388 suitable for ISO taper size 50	308830 50
Pull stud 90° sealed suitable for steep tapers 50	308795 50
Torque insert for Pull studs to SO 7388 suitable for ISO taper size 50	308812 50