



## Reducing adapter SK / MT for locking threads, form A, BT 50, MT internal: 4



### Order data

Order number	303097 4
GTIN	4062406109448
Item class	32A

### Description

**Version:**

Ground internally and externally.

**Application:**

For clamping tools **with MT shank.**

**Optional extras:**

Pull studs (PS) No. 308760 – 308806.

Concentricity:  $\leq 8 \mu\text{m}$

Overhang dimension A: 70 mm

External  $\varnothing$  D: 48 mm

### Technical description

Overhang dimension A	70 mm
External $\varnothing$ D	48 mm
Adapter	BT 50
Standard	DIN 6383
Arbor standard	ISO 7388-2
Arbor standard	JIS B6339
Shape	A

Balance quality G at rotational speed	G 6.3 at 15,000 rpm
Concentricity	≤ 8 μm
Type of product	Arbor adapter

## Accessories

Pull stud 45° sealed suitable for steep tapers 50	308765 50
Pull stud 90° sealed suitable for steep tapers 50	308790 50
Torque insert for Pull studs to SO 7388 suitable for ISO taper size 50	308812 50
Torque insert for Pull studs to DIN 69872 suitable for ISO taper size 50	308810 50
Pull stud 45° sealed suitable for steep tapers 50	308760 50
Wrench for pull studs DIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 50	308820 50
Pull stud 90° sealed suitable for steep tapers 50	308795 50
Pull-stud 60° sealed suitable for steep tapers 50	308780 50
Pull stud 60° sealed suitable for steep tapers 50	308785 50
Wrench for pull studs ISO 7388 suitable for ISO taper size 50	308830 50