



Reducing adapter SK / MT for locking threads, form A, BT 40, MT internal: 4



Order data

| | |
|--------------|---------------|
| Order number | 303092 4 |
| GTIN | 4062406109417 |
| Item class | 32A |

Description

Version:

Ground internally and externally.

Application:

For clamping tools **with MT shank.**

Optional extras:

Pull studs (PS) No. 308760 – 308806.

Concentricity: $\leq 8 \mu\text{m}$

Overhang dimension A: 95 mm

External \varnothing D: 48 mm

Technical description

| | |
|---------------------------------------|---------------------|
| Overhang dimension A | 95 mm |
| External \varnothing D | 48 mm |
| Adapter | BT 40 |
| Standard | DIN 6383 |
| Arbor standard | ISO 7388-2 |
| Arbor standard | JIS B6339 |
| Shape | A |
| Balance quality G at rotational speed | G 6.3 at 15,000 rpm |

| | |
|-----------------|---------------|
| Concentricity | ≤ 8 µm |
| Type of product | Arbor adapter |

Accessories

| | |
|--|-----------|
| Wrench for pull studs ISO 7388 suitable for ISO taper size 40 | 308830 40 |
| Pull-stud 60° sealed suitable for steep tapers 40 | 308780 40 |
| Pull stud Hurco 45° with fit sealed suitable for steep tapers 40 | 308802 40 |
| Pull stud 45° sealed suitable for steep tapers 40 | 308760 40 |
| Pull stud 90° sealed suitable for steep tapers 40 | 308795 40 |
| Pull stud Hurco 90° with bore and fit sealed suitable for steep tapers 40 | 308805 40 |
| Pull stud Hurco 90° with fit sealed suitable for steep tapers 40 | 308806 40 |
| Pull stud 60° sealed suitable for steep tapers 40 | 308785 40 |
| Wrench for pull studs DIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40 | 308820 40 |
| Torque insert for Pull studs to DIN 69872 suitable for ISO taper size 40 | 308810 40 |
| Pull stud Hurco 45° with bore and fit sealed suitable for steep tapers 40 | 308801 40 |
| Pull stud 45° sealed suitable for steep tapers 40 | 308765 40 |
| Hurco 60° pull stud with bore and fit sealed suitable for steep tapers 40 | 308803 40 |
| Torque insert for Pull studs to SO 7388 suitable for ISO taper size 40 | 308812 40 |
| Pull stud 90° sealed suitable for steep tapers 40 | 308790 40 |
| Pull stud Hurco 60° with fit sealed suitable for steep tapers 40 | 308804 40 |