

Garant GRIDLINE

Side panel, Drawer 24G deep, suitable for column frame height: 2500mm**Order data**

| | |
|--------------|---------------|
| Order number | 935511 2500 |
| GTIN | 4062406108779 |
| Item class | 9GK |

Description**Application:**

To cover the fronts of the side walls, sheet metal angle plate, 30 mm wide.

Colour:

Light grey RAL 7035, **powder-coated**.

Note:

If a side panel is used, you need only a sheet metal panel No. 935040; 935045 or end bridging rail No. 935442; 935462 on the inside of the column frame.

For reasons of stability we recommend that side panels should be fitted at the left and right ends of the rack.

Technical description

| | |
|----------------------------------|--|
| suitable for column frame height | 2500 mm |
| Application range | Drawer/shelf combination unit |
| Material thickness | 1.2 mm |
| Colour selection | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |

| | |
|------------------------|-----------------|
| Product name attribute | Drawer 24G deep |
| Depth | 710 mm |
| Type of product | Side panel |