

Garant GRIDLINE

Side panel, Drawer 20G deep, suitable for column frame height: 2500mm**Order data**

Order number	935510 2500
GTIN	4062406109578
Item class	9GK

Description**Application:**

To cover the fronts of the side walls, sheet metal angle plate, 30 mm wide.

Colour:

Light grey RAL 7035, **powder-coated**.

Note:

If a side panel is used, you need only a sheet metal panel No. 935040; 935045 or end bridging rail No. 935442; 935462 on the inside of the column frame.

For reasons of stability we recommend that side panels should be fitted at the left and right ends of the rack.

Technical description

suitable for column frame height	2500 mm
Application range	Drawer/shelf combination unit
Material thickness	1.2 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Product name attribute	Drawer 20G deep
Depth	610 mm
Type of product	Side panel