



ER collet chuck Form AD, SK 50 A = 160, for ER collet size: 25



Order data

Order number	300615 25
GTIN	4062406109622
Item class	32A

Description

Version:

Taper ground internally and externally. With Balluff/RFID chip bore.

HOLEX –

HOLEX precision clamping nut, balanced (G6.3 / 18,000 rpm, all shanks fine bead blasted. Balancing quality G6.3 / 18,000 rpm).

Application:

For clamping tools with plain shank in collets to DIN 6499 – Form A and B.

Supplied with:

Clamping nut.

Optional extras:

Pull studs (PS) No. 308600 – 308806, PS pull stud wrenches No.308820 – 308835, ER chuck key No. 309680 – 613300, ER collets No. 308901 – 309449, ER clamping nuts No. 309615 (for sealing rings), sealing rings No. 309625 – 309645 (for No. 309615).

Machining strategy: HSC

Clamping range: 1 - 16 mm

Overhang dimension A: 160 mm

External Ø D: 42 mm

Spare GARANT high-speed clamping nut No. 309610: 25

Spare HOLEX nut No. 309580: 25

Technical description

External Ø D	42 mm
Spare GARANT high-speed clamping nut No. 309610	25

Spare HOLEX nut No. 309580	25
Overhang dimension A	160 mm
Clamping range	1 - 16 mm
Clamping $\varnothing D_1$	1-16 mm
Adapter	SK 50 A = 160
Arbor standard	ISO 7388-1
Shape	AD
Balance quality G at rotational speed	G 6.3 at 18,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HSC
Balluffchip bore	yes
Type of product	Collet chuck

Accessories

ER collet for machine taps with seal Nominal clamping $\varnothing d$ 8 mm	309411 8
ER collet for machine taps with seal Nominal clamping $\varnothing d$ 7 mm	309409 7
ET collet with radial compensation for tapping and reaming Nominal clamping $\varnothing d$ 9 mm	309447 9
Special pull stud with internal thread suitable for steep tapers 50	308740 50
ER collet with seal and spray nozzles Nominal clamping $\varnothing d$ 10 mm	308962 10
ER collet with seal and spray nozzles Nominal clamping $\varnothing d$ 16 mm	308962 16
ER collet for machine taps with seal and spray nozzles Nominal clamping $\varnothing d$ 8 mm	309413 8
ER clamping nut for ER 25	309580 25
ER collet Nominal clamping $\varnothing d$ 6 mm	308941 6

ER collet Nominal clamping Ø d 11 mm	308960 11
ER collet with seal Nominal clamping Ø d 5 mm	308959 5
ER collet Nominal clamping Ø d 15 mm	308941 15
ER collet with seal and spray nozzles Nominal clamping Ø d 5 mm	308962 5
ER collet with seal and spray nozzles Nominal clamping Ø d 4 mm	308962 4
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 5 mm	309447 5
ER collet with seal Nominal clamping Ø d 13 mm	308946 13
ER collet with seal Nominal clamping Ø d 10 mm	308946 10
ER collet Nominal clamping Ø d 12 mm	308960 12
ER collet for machine taps with seal Nominal clamping Ø d 10 mm	309411 10
ER collet Nominal clamping Ø d 2 mm	308941 2
ER chuck key for ER collet chuck 25	309680 25
ER collet for machine taps with seal Nominal clamping Ø d 16 mm	309411 16
ER collet with seal Nominal clamping Ø d 10 mm	308959 10
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 3,5 mm	309430 3,5
ER collet with seal Nominal clamping Ø d 14 mm	308959 14
ER collet Nominal clamping Ø d 5 mm	308941 5
ER collet with seal and spray nozzles Nominal clamping Ø d 11 mm	308962 11
ER collet Nominal clamping Ø d 2 mm	308960 2
ER plain bearing clamping nut for ER 25	309612 25
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 3,5 mm	309447 3,5
Special pull stud with no internal thread sealed suitable for steep tapers 50	308720 50
ER collet Nominal clamping Ø d 3 mm	308960 3

ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 14 mm	309413 14
ER collet with seal Nominal clamping Ø d 12 mm	308959 12
ER collet for machine taps with seal Nominal clamping Ø d 12 mm	309411 12
ER collet with seal and spray nozzles Nominal clamping Ø d 7 mm	308962 7
ER collet Nominal clamping Ø d 2,5 mm	308941 2,5
ER collet with seal Nominal clamping Ø d 3 mm	308946 3
ER collet Nominal clamping Ø d 10 mm	308960 10
Pull stud sealed, form B suitable for steep tapers 50	308650 50
ER collet with seal Nominal clamping Ø d 16 mm	308959 16
Pull stud sealed, form B suitable for steep tapers 50	308620 50
ER collet with seal and spray nozzles Nominal clamping Ø d 12 mm	308962 12
ER collet with seal Nominal clamping Ø d 12 mm	308946 12
ER collet with seal and spray nozzles Nominal clamping Ø d 8 mm	308962 8
ER collet with seal Nominal clamping Ø d 11 mm	308946 11
Torque wrench with reversible ratchet maximum torque 200 N·m	656050 200
ER collet with seal Nominal clamping Ø d 15 mm	308946 15
ER collet Nominal clamping Ø d 7 mm	308960 7
ER collet for machine taps with seal Nominal clamping Ø d 12 mm	309409 12
ER collet for machine taps with seal Nominal clamping Ø d 16 mm	309409 16
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 6 mm	309430 6
ER collet with seal Nominal clamping Ø d 3 mm	308959 3
ER collet for machine taps with seal Nominal clamping Ø d 4,5 mm	309409 4,5
	309413 10

ER collet for machine taps with seal and spray nozzles
Nominal clamping \varnothing d 10 mm

ER collet Nominal clamping \varnothing d 6 mm	308960 6
ER clamping nut High Speed for ER 25	309610 25
ER collet for machine taps with seal Nominal clamping \varnothing d 4,5 mm	309411 4,5
ER collet Nominal clamping \varnothing d 13 mm	308960 13
ER collet for machine taps with seal Nominal clamping \varnothing d 14 mm	309411 14
ER collet with seal and spray nozzles Nominal clamping \varnothing d 9 mm	308962 9
ER collet Nominal clamping \varnothing d 12 mm	308941 12
ER collet Nominal clamping \varnothing d 9 mm	308941 9
ER collet Nominal clamping \varnothing d 8 mm	308941 8
ER collet with seal Nominal clamping \varnothing d 8 mm	308946 8
Pull stud sealed, form A suitable for steep tapers 50	308610 50
ER collet with seal and spray nozzles Nominal clamping \varnothing d 3 mm	308962 3
ET collet for thread tapping, with axial compensation Nominal clamping \varnothing d 2,8 mm	309430 2,8
Torque insert for Pull studs to SO 7388 suitable for ISO taper size 50	308812 50
ER collet Nominal clamping \varnothing d 16 mm	308941 16
ER collet with seal Nominal clamping \varnothing d 11 mm	308959 11
ER collet Nominal clamping \varnothing d 11 mm	308941 11
ER collet Nominal clamping \varnothing d 14 mm	308960 14
ER collet Nominal clamping \varnothing d 9 mm	308960 9
ER collet with seal Nominal clamping \varnothing d 15 mm	308959 15
ER collet with seal Nominal clamping \varnothing d 16 mm	308946 16
ET collet for thread tapping, with axial compensation Nominal clamping \varnothing d 4,5 mm	309430 4,5
	309430 7

ET collet for thread tapping, with axial compensation
Nominal clamping \varnothing d 7 mm

ER collet Nominal clamping \varnothing d 3 mm	308941 3
Pull stud 60° sealed suitable for steep tapers 50	308785 50
Wrench for pull studs ISO 7388 suitable for ISO taper size 50	308830 50
Pull stud 45° sealed suitable for steep tapers 50	308765 50
ER clamping nut for HiRunER collet chucks for ER 25	309617 25
Pull stud Form A suitable for steep tapers 50	308600 50
ER collet Nominal clamping \varnothing d 8 mm	308960 8
Torque insert for Pull studs to DIN 69872 suitable for ISO taper size 50	308810 50
ER collet for machine taps with seal and spray nozzles Nominal clamping \varnothing d 4,5 mm	309413 4,5
Pull stud 90° sealed suitable for steep tapers 50	308790 50
ER collet Nominal clamping \varnothing d 16 mm	308960 16
Pull stud sealed suitable for steep tapers 50	308660 50
ER collet for machine taps with seal and spray nozzles Nominal clamping \varnothing d 9 mm	309413 9
ET collet with radial compensation for tapping and reaming Nominal clamping \varnothing d 7 mm	309447 7
ER collet Nominal clamping \varnothing d 5 mm	308960 5
ER collet for machine taps with seal Nominal clamping \varnothing d 6 mm	309411 6
ER collet with seal Nominal clamping \varnothing d 7 mm	308946 7
Wrench for pull studs DIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 50	308820 50
ET collet with radial compensation for tapping and reaming Nominal clamping \varnothing d 8 mm	309447 8
ER collet with seal Nominal clamping \varnothing d 9 mm	308946 9
ER collet with seal Nominal clamping \varnothing d 6 mm	308959 6
Pull stud 90° sealed suitable for steep tapers 50	308795 50

ER collet Nominal clamping Ø d 10 mm	308941 10
ER collet with seal Nominal clamping Ø d 13 mm	308959 13
ER collet with seal Nominal clamping Ø d 9 mm	308959 9
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 10 mm	309430 10
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 9 mm	309430 9
ER collet Nominal clamping Ø d 4 mm	308960 4
ER collet with seal Nominal clamping Ø d 5 mm	308946 5
ER collet for machine taps with seal Nominal clamping Ø d 9 mm	309411 9
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 10 mm	309447 10
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 4,5 mm	309447 4,5
ER collet for machine taps with seal Nominal clamping Ø d 11 mm	309411 11
ER collet with seal Nominal clamping Ø d 4 mm	308946 4
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 12 mm	309413 12
ER collet with seal and spray nozzles Nominal clamping Ø d 15 mm	308962 15
Special pull stud with no internal thread sealed suitable for steep tapers 50	308700 50
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 4 mm	309447 4
Pull stud 45° sealed suitable for steep tapers 50	308760 50
ER collet with seal and spray nozzles Nominal clamping Ø d 13 mm	308962 13
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 6 mm	309413 6
ER collet with seal Nominal clamping Ø d 6 mm	308946 6
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 7 mm	309413 7

ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 3 mm	309447 3
ER collet Nominal clamping Ø d 14 mm	308941 14
ER collet for machine taps with seal Nominal clamping Ø d 9 mm	309409 9
ER collet Nominal clamping Ø d 15 mm	308960 15
ER collet for machine taps with seal Nominal clamping Ø d 14 mm	309409 14
ER collet Nominal clamping Ø d 13 mm	308941 13
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 11 mm	309413 11
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 8 mm	309430 8
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 6 mm	309447 6
ER collet for machine taps with seal Nominal clamping Ø d 8 mm	309409 8
ER collet for machine taps with seal Nominal clamping Ø d 7 mm	309411 7
ER collet with seal Nominal clamping Ø d 4 mm	308959 4
ER collet with seal Nominal clamping Ø d 14 mm	308946 14
Pull stud, 18CrNiMo7 sealed, form B suitable for steep tapers 50	308615 50
ER collet with seal and spray nozzles Nominal clamping Ø d 6 mm	308962 6
ER collet for machine taps with seal Nominal clamping Ø d 10 mm	309409 10
ER collet with seal Nominal clamping Ø d 8 mm	308959 8
ER collet for machine taps with seal Nominal clamping Ø d 6 mm	309409 6
ER collet with seal Nominal clamping Ø d 7 mm	308959 7
ER collet Nominal clamping Ø d 7 mm	308941 7
ER collet Nominal clamping Ø d 4 mm	308941 4

ER collet for machine taps with seal Nominal clamping \varnothing d 11 mm	309409 11
Pull stud, 18CrNiMo7 Form A suitable for steep tapers 50	308605 50
Pull stud Form B suitable for steep tapers 50	308640 50
ER collet with seal and spray nozzles Nominal clamping \varnothing d 14 mm	308962 14