

Garant GRIDLINE

**Drawer, 12×20G, Drawer front height: 100mm****Order data**

Order number	927500 100
GTIN	4062406109790
Item class	9GG

**Description****Version:**

100% full extension drawers in sturdy steel construction, with differential runners and 75 kg load capacity. Aluminium handles with labelling strips that can be exchanged and rewritten. New type of drawer concept for optimum equipment with modular dividing material.

**Suitable for:**

All cabinet casings 16G.

**Colour:**

Drawer unit body RAL 7035 light grey, drawers RAL 7016 anthracite **powder-coated**. **Drawer body not configurable, always RAL 7035 light grey.**

**Technical description**

Drawer/pull-out shelf load capacity	75 kg
Usable height	75 mm
Front height	100 mm
Weight	7.5 kg
Drawer usable area in G	12×20
Usable width in G	12
Usable depth in G	20
Application range	Workbench casing
Usable depth	500 mm

Usable width	300 mm
with individual drawer release system	no
Material thickness	1 mm
Drawer runner extension (partial/full extension)	100 %
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	12×20G
Type of product	Drawer