

Garant GRIDLINE**Casing 16G with door hinged on the right, for individual configuration with drawers, 12×20G, Height / door height: 800/525mm****Order data**

Order number	927420 800/525
GTIN	4062406109677
Item class	9GG

**Description****Version:**

16G cabinet casing with door, for individual configuration with drawers, in sturdy steel construction. Can be locked centrally with a cylinder lock.

Door hinged on the right.

**Fitted with:**

Number of height-adjustable storage shelves: 1

**Colour:**

Body RAL 7035 light grey, door RAL 7016 anthracite **powder-coated**.

**Note:**

When equipping the cabinet with drawers, check that the sum of the individual drawer front heights adds up to the usable cabinet height.

Sizes 600/425 and 700/525 suitable only for Ready-to-go workbenches.

**Technical description**

Usable width	350 mm
Door stop	right-hand

Usable height for drawers	150 mm
Height	800 mm
Door height	525 mm
Depth	650 mm
Weight	27.1 kg
Door usable height	525 mm
Number of height-adjustable shelves	1
Number of doors	1
Width	400 mm
Width in G	12
Depth in G	20
Version	for individual configuration
Material thickness	1 mm
Door opening angle	180 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	12x20G
Type of product	Workbench casing

## Accessories

Shelf carriers for shelves of workbenches Type 12	927094 12
Slide handle for GridLine Type KO12	914226 KO12
Fixed shelf, galvanised Type 1	927515 1
Lock plate for GridLine Type KO21	914227 KO21