

Garant GRIDLINE

16G cabinet casing, mobile, for individual configuration with drawers, 12x20G, Height of the housing: 400mm



Order data

Order number	927430 400
GTIN	4062406109714
Item class	9GG

Description

Version:

16G cabinet casing, mobile, for individual configuration with drawers, in sturdy steel construction. With ABS plastic shelf and 2-component Haptoprene® push handles. With 2 ball-bearing fixed wheels and 2 castors Ø 125 mm, with treadless polyurethane tyres. Castors with brakes for the wheels and the castor heads. Can be locked centrally with a cylinder lock.

Colour:

Light grey RAL 7035, **powder-coated**.

Note:

When equipping the cabinet with drawers, check that the sum of the individual drawer front heights adds up to the usable cabinet height.

The cabinet casing may be equipped only with drawers No. 927505!

Do not slide under electric height-adjustable workstations No. 920301 – 920316.

Technical description

with anti-roll lip	yes
Electronic locking system can be retrofitted	yes

Number of fixed wheels without parking brake	2
Treadless tyres	yes
Width	400 mm
Height	600 mm
ComfortClose	no
Wheel Ø	125 mm
Number of castors with parking brake	2
Weight	20.9 kg
Number of drawers	0
maximum load capacity	600 kg
Drawer body usable height	325 mm
Number of doors	0
Usable height	325 mm
Depth	650 mm
Version	wheeled
Version	for individual configuration
Usable height for drawers	325 mm
Casing open at the top	no
Number of pull-out shelves	0
Material thickness	1 mm
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	12x20G
Type of product	Workshop mobile drawer unit

Accessories

Lock plate for GridLine Type KO21

914227 KO21