

Garant GRIDLINE

Drawer, 12×20G, Drawer front height: 300mm**Order data**

Order number	927500 300
GTIN	4062406109844
Item class	9GG

Description**Version:**

100% full extension drawers in sturdy steel construction, with differential runners and 75 kg load capacity. Aluminium handles with labelling strips that can be exchanged and rewritten. New type of drawer concept for optimum equipment with modular dividing material.

Suitable for:

All cabinet casings 16G.

Colour:

Drawer unit body RAL 7035 light grey, drawers RAL 7016 anthracite **powder-coated**. **Drawer body not configurable, always RAL 7035 light grey.**

Technical description

Usable height	275 mm
Drawer/pull-out shelf load capacity	75 kg
Weight	10.6 kg
Front height	300 mm
Drawer usable area in G	12×20
Usable width in G	12

Usable depth in G	20
Application range	Workbench casing
Usable depth	500 mm
Usable width	300 mm
with individual drawer release system	no
Material thickness	1 mm
Drawer runner extension (partial/full extension)	100 %
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	12×20G
Type of product	Drawer