

Garant GRIDLINE

**Drawer, 12×20G, Drawer front height: 200mm****Order data**

Order number	927500 200
GTIN	4062406109820
Item class	9GG

**Description****Version:**

100% full extension drawers in sturdy steel construction, with differential runners and 75 kg load capacity. Aluminium handles with labelling strips that can be exchanged and rewritten. New type of drawer concept for optimum equipment with modular dividing material.

**Suitable for:**

All cabinet casings 16G.

**Colour:**

Drawer unit body RAL 7035 light grey, drawers RAL 7016 anthracite **powder-coated**. **Drawer body not configurable, always RAL 7035 light grey.**

**Technical description**

Drawer/pull-out shelf load capacity	75 kg
Front height	200 mm
Weight	9.1 kg
Usable height	175 mm
Drawer usable area in G	12×20
Usable depth in G	20
Usable width in G	12

Application range	Workbench casing
Usable width	300 mm
Usable depth	500 mm
with individual drawer release system	no
Material thickness	1 mm
Drawer runner extension (partial/full extension)	100 %
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	12×20G
Type of product	Drawer