

Garant GRIDLINE

Drawer casing 24G with drawers, 20×20G, Height / number of drawers: 200/1



Order data

Order number	927600 200/1
GTIN	4062406109936
Item class	9GG

Description

Version:

Drawer cabinet with sturdy steel construction. **100% full extension drawers** with differential runners and 75 kg load capacity. **Aluminium handles** with labelling strips that can be exchanged and rewritten. Can be locked centrally with cylinder lock.

Fitted with:

Drawer front height, mm: 125

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Technical description

Weight	19.1 kg
Depth	650 mm
Number of doors	0
Drawer usable depth	500 mm
Drawer usable depth in G	20
Drawer front height	125 mm
Usable height for drawers	125 mm
Drawer usable width	500 mm
Number of drawers	1

Drawer usable width in G	20
Usable width	550 mm
Width	600 mm
Drawer usable area in G	20×20
Usable height	125 mm
Height	200 mm
Number of pull-out shelves	0
Material thickness	1 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer runner extension (partial/full extension)	100 %
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	Workbench casing

Accessories

Drawer Drawer front height 125 mm	927800 125
Screw set for GridLine workbenches Type 1	927093 1
24G casing for individual configuration with drawers Height 200 mm	927720 200
Lock plate for GridLine Type KO21	914227 KO21
Handle end caps 20 pieces Type 10	951025 10