

Garant GRIDLINE

**Drawer with one-handed individual drawer release system, 12×20G, Drawer front height: 200mm****Order data**

Order number	927505 200
GTIN	4062406109905
Item class	9GG

**Description****Version:**

100% full extension drawers in sturdy steel construction, with differential runners and 75 kg load capacity. Aluminium handles with labelling strips that can be exchanged and rewritten. New type of drawer concept for optimum equipment with modular dividing material.

With **one-handed individual drawer release system** prevents the opening of drawers during transport. Essential for all roller cabinets and mobile workbenches and cabinet casings.

**Suitable for:**

All cabinet casings 16G.

**Colour:**

Drawer unit body RAL 7035 light grey, drawers RAL 7016 anthracite **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

**Technical description**

Weight	9.2 kg
Usable height	175 mm
Front height	200 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer usable area in G	12×20

Individual drawer release system	One-hand
Usable width in G	12
Usable depth in G	20
Application range	Assembly trolley
Usable width	300 mm
Usable depth	500 mm
with individual drawer release system	yes
Material thickness	1 mm
Drawer runner extension (partial/full extension)	100 %
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	12×20G
Type of product	Drawer

## Accessories

One-hand individual drawer release system Drawer usable width in G 12	951020 12
-----------------------------------------------------------------------	-----------