

Garant GRIDLINE

Drawer casing 24G with drawers, 20×20G, Height / number of drawers: 900/5**Order data**

Order number	927600 900/5
GTIN	4062406110130
Item class	9GG

Description**Version:**

Drawer cabinet with sturdy steel construction. **100% full extension drawers** with differential runners and 75 kg load capacity. **Aluminium handles** with labelling strips that can be exchanged and rewritten. Can be locked centrally with cylinder lock.

Fitted with:

Drawer front height, mm: 75, 75, 150, 200, 300

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Technical description

Width	600 mm
Usable height for drawers	800 mm
Weight	74 kg
Number of drawers	5
Drawer usable area in G	20×20

Usable width	550 mm
Height	900 mm
Drawer front height	300 mm
Drawer front height	200 mm
Drawer front height	150 mm
Drawer front height	75 mm
Drawer front height	75 mm
Drawer usable width in G	20
Drawer usable width	500 mm
Drawer usable depth in G	20
Number of doors	0
Drawer usable depth	500 mm
Depth	650 mm
Usable height	800 mm
Number of pull-out shelves	0
Material thickness	1 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer runner extension (partial/full extension)	100 %
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	Workbench casing

Accessories

Drawer Drawer front height 75 mm	927800 75
Drawer Drawer front height 300 mm	927800 300

Drawer Drawer front height 200 mm	927800 200
Drawer Drawer front height 150 mm	927800 150
24G casing for individual configuration with drawers Height 900 mm	927720 900
Lock plate for GridLine Type KO21	914227 KO21
Handle end caps 20 pieces Type 10	951025 10