

Garant GRIDLINE

Casing 24G with door hinged on the right / drawers, 20×20G, Height / number of drawers: 800/2**Order data**

Order number	927610 800/2
GTIN	4062406110260
Item class	9GG

Description**Version:**

Drawer cabinet with sturdy steel construction. **100% full extension drawers** with differential runners and 75 kg load capacity. **Aluminium handles** with labelling strips that can be exchanged and rewritten. Can be locked centrally with cylinder lock.

Door hinged on the right.

Fitted with:

Drawer front height, mm: 75#75

Door height, mm: 525

Number of height-adjustable storage shelves: 1

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

Sizes 600 and 700 suitable only for Ready-to-go workbenches.

Technical description

Door stop	right-hand
-----------	------------

Drawer front height	75 mm
Drawer front height	75 mm
Usable height for drawers	150 mm
Usable width	550 mm
Door usable height	525 mm
Drawer usable depth in G	20
Number of doors	1
Weight	50 kg
Door height	525 mm
Depth	650 mm
Drawer usable depth	500 mm
Height	800 mm
Drawer usable width in G	20
Number of drawers	2
Width	600 mm
Drawer usable area in G	20×20
Drawer usable width	500 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer runner extension (partial/full extension)	100 %
Door opening angle	180 degrees
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	Workbench casing

Accessories

Drawer Drawer front height 75 mm	927800 75
----------------------------------	-----------

Slide handle for GridLine Type KO12	914226 KO12
Casing 24G with door hinged on the right, for individual configuration with drawers Height / door height 800/525 mm	927725 800/525
Lock plate for GridLine Type KO21	914227 KO21
Handle end caps 20 pieces Type 10	951025 10