

Garant GRIDLINE

Casing 24G with door hinged on the right / drawers, 20×20G, Height / number of drawers: 900/2**Order data**

Order number	927610 900/2
GTIN	4062406110277
Item class	9GG

Description**Version:**

Drawer cabinet with sturdy steel construction. **100% full extension drawers** with differential runners and 75 kg load capacity. **Aluminium handles** with labelling strips that can be exchanged and rewritten. Can be locked centrally with cylinder lock.

Door hinged on the right.

Fitted with:

Drawer front height, mm: 75#75

Door height, mm: 625

Number of height-adjustable storage shelves: 1

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

Sizes 600 and 700 suitable only for Ready-to-go workbenches.

Technical description

Drawer usable width in G	20
--------------------------	----

Door height	625 mm
Usable height for drawers	150 mm
Door usable height	625 mm
Number of drawers	2
Width	600 mm
Drawer usable depth in G	20
Drawer usable width	500 mm
Height	900 mm
Drawer front height	75 mm
Drawer front height	75 mm
Number of doors	1
Depth	650 mm
Drawer usable depth	500 mm
Weight	52 kg
Drawer usable area in G	20×20
Door stop	right-hand
Usable width	550 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer runner extension (partial/full extension)	100 %
Door opening angle	180 degrees
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	Workbench casing

Accessories

Drawer Drawer front height 75 mm

927800 75

Slide handle for GridLine Type KO12	914226 KO12
Casing 24G with door hinged on the right, for individual configuration with drawers Height / door height 900/625 mm	927725 900/625
Lock plate for GridLine Type KO21	914227 KO21
Handle end caps 20 pieces Type 10	951025 10