

Garant GRIDLINE

## Drawer casing 24G with drawers, 20×20G, Height / number of drawers: 300/2



### Order data

Order number	927600 300/2
GTIN	4062406215828
Item class	9GG

### Description

#### Version:

Drawer cabinet with sturdy steel construction. **100% full extension drawers** with differential runners and 75 kg load capacity. **Aluminium handles** with labelling strips that can be exchanged and rewritten. Can be locked centrally with cylinder lock.

#### Fitted with:

Drawer front height, mm: 75#150

#### Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

### Technical description

Drawer usable width in G	20
Number of drawers	2
Usable height for drawers	225 mm
Usable height	225 mm
Width	600 mm
Usable width	550 mm
Depth	650 mm
Drawer usable area in G	20×20

Drawer usable width	500 mm
Drawer front height	150 mm
Drawer front height	75 mm
Drawer usable depth	500 mm
Weight	30 kg
Height	300 mm
Drawer usable depth in G	20
Number of doors	0
Number of pull-out shelves	0
Material thickness	1 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer runner extension (partial/full extension)	100 %
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x20G
Type of product	Workbench casing

## Accessories

Drawer Drawer front height 150 mm	927800 150
Drawer Drawer front height 75 mm	927800 75
Screw set for GridLine workbenches Type 1	927093 1
24G casing for individual configuration with drawers Height 300 mm	927720 300
Lock plate for GridLine Type KO21	914227 KO21
Handle end caps 20 pieces Type 10	951025 10