

Garant GRIDLINE

## Drawer casing 24G with drawers, 20×20G, Height / number of drawers: 900/6



### Order data

Order number	927600 900/6
GTIN	4062406215842
Item class	9GG

### Description

#### Version:

Drawer cabinet with sturdy steel construction. **100% full extension drawers** with differential runners and 75 kg load capacity. **Aluminium handles** with labelling strips that can be exchanged and rewritten. Can be locked centrally with cylinder lock.

#### Fitted with:

Drawer front height, mm: 75, 100, 100, 125, 150, 250

#### Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

### Technical description

Drawer usable width	500 mm
Weight	81 kg
Drawer usable area in G	20×20
Drawer front height	100 mm
Drawer front height	75 mm

Drawer front height	250 mm
Drawer front height	150 mm
Drawer front height	125 mm
Drawer front height	100 mm
Usable height	800 mm
Width	600 mm
Usable width	550 mm
Drawer usable width in G	20
Drawer usable depth	500 mm
Number of doors	0
Drawer usable depth in G	20
Number of drawers	6
Depth	650 mm
Height	900 mm
Usable height for drawers	800 mm
Number of pull-out shelves	0
Material thickness	1 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer runner extension (partial/full extension)	100 %
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x20G
Type of product	Workbench casing

## Accessories

Drawer Drawer front height 100 mm	927800 100
-----------------------------------	------------

Drawer Drawer front height 150 mm	927800 150
Drawer Drawer front height 125 mm	927800 125
Drawer Drawer front height 250 mm	927800 250
Drawer Drawer front height 75 mm	927800 75
24G casing for individual configuration with drawers Height 900 mm	927720 900
Lock plate for GridLine Type KO21	914227 KO21
Handle end caps 20 pieces Type 10	951025 10