

Garant GRIDLINE

Central locking for standard heights, Type: 1**Order data**

Order number	935590 1
GTIN	4062406110239
Item class	9GK

Description**NOTE: Colour selection possible****Version:**

Consisting of a lock plate with **cylinder lock** with 2 keys and locking bars, complete for storage shelves No. 935110 – 935121 for bay depth 20G, complete for storage shelves No. 935130 - 935161 for bay depth 24G.

Available for the following standard usable heights:

700 / 800 / 900 / 1000 / 1250 / 1500 mm.

Note:

- **If drawers/pull-out shelves are fitted central locking is necessary to prevent more than one drawer being opened at a time.**
- **Central locking cannot be retrofitted at a later stage.**
- **When ordering, please supply a sketch of the desired arrangement of shelves.**
- **Maximum width 1900 mm.**

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Technical description

Special features	Cannot be retrofitted
------------------	-----------------------

Supplied complete with cylinder lock with 2 keys and locking bars	yes
Standard usable height for central locking 600/ 700/ 750/ 900/ 1050/ 1225/ 1350/ 1525 mm	yes
Application range	Drawer/shelf combination unit
Material thickness	1.2 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Central locking

Accessories

Lock plate for Group 94 workbench drawer units without cylinder insert	914236
------------------------------------------------------------------------	--------