

Garant GRIDLINE

Central locking for standard heights, Type: 1**Order data**

| | |
|--------------|---------------|
| Order number | 935590 1 |
| GTIN | 4062406110239 |
| Item class | 9GK |

Description**Version:**

Consisting of a lock plate with **cylinder lock** with 2 keys and locking bars, complete for storage shelves No. 935110 – 935121 for bay depth 20G, complete for storage shelves No. 935130 - 935161 for bay depth 24G.

For the following **standard heights**:

700 / 800 / 900 / 1000 / 1250 / 1500 mm.

Or for the following **standard usable heights**:

600 / 700 / 800 / 900 / 1150 / 1400 mm.

Note:

- **If drawers/pull-out shelves are fitted central locking is necessary to prevent more than one drawer being opened at a time.**
- **Central locking cannot be retrofitted at a later stage.**
- **When ordering, please supply a sketch of the desired arrangement of shelves.**
- **Maximum width 1900 mm.**

Technical description

| | |
|------------------|-----------------------|
| Special features | Cannot be retrofitted |
|------------------|-----------------------|

| | |
|--|--|
| Supplied complete with cylinder lock with 2 keys and locking bars | yes |
| Standard usable height for central locking 600/ 700/ 750/ 900/ 1050/ 1225/ 1350/ 1525 mm | yes |
| Application range | Drawer/shelf combination unit |
| Material thickness | 1.2 mm |
| Cylinder lock | modular barrel |
| Colour selection | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Type of product | Central locking |

Accessories

| | |
|--|--------|
| Lock plate for Group 94 workbench drawer units without cylinder insert | 914236 |
|--|--------|