

Garant GRIDLINE

Casing 24G with door hinged on the right, Height / number of drawers: 700**Order data**

| | |
|--------------|---------------|
| Order number | 927615 700 |
| GTIN | 4062406110307 |
| Item class | 9GG |

Description**Version:**

Drawer cabinet with sturdy steel construction. **100% full extension drawers** with differential runners and 75 kg load capacity. **Aluminium handles** with labelling strips that can be exchanged and rewritten. Can be locked centrally with cylinder lock. Door hinged on the right.

Fitted with:

Door height, mm: 625

Number of height-adjustable storage shelves: 1

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

Sizes 600 and 700 suitable only for Ready-to-go workbenches.

Technical description

| | |
|-------------------|-------|
| Weight | 28 kg |
| Number of drawers | 0 |

| | |
|--------------------------------------------------|-------------------------------------------------------------------|
| Depth | 650 mm |
| Width | 600 mm |
| Door height | 625 mm |
| Door stop | right-hand |
| Usable height | 625 mm |
| Number of doors | 1 |
| Height | 700 mm |
| Door usable height | 625 mm |
| Usable width | 550 mm |
| Drawer/pull-out shelf load capacity | 75 kg |
| Drawer runner extension (partial/full extension) | 100 % |
| Door opening angle | 180 degrees |
| Cylinder lock | modular barrel |
| Colour selection | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Type of product | Workbench casing |

Accessories

| | |
|-------------------------------------|-------------|
| Slide handle for GridLine Type KO12 | 914226 KO12 |
|-------------------------------------|-------------|