

Garant GRIDLINE

Casing 24G with door hinged on the right, Height / number of drawers: 900**Order data**

Order number	927615 900
GTIN	4062406110321
Item class	9GG

Description**Version:**

Drawer cabinet with sturdy steel construction. **100% full extension drawers** with differential runners and 75 kg load capacity. **Aluminium handles** with labelling strips that can be exchanged and rewritten. Can be locked centrally with cylinder lock.

Door hinged on the right.

Fitted with:

Door height, mm: 800

Number of height-adjustable storage shelves: 1

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

Sizes 600 and 700 suitable only for Ready-to-go workbenches.

Technical description

Door stop	right-hand
Depth	650 mm

Usable height	800 mm
Width	600 mm
Weight	34 kg
Height	900 mm
Number of doors	1
Door height	800 mm
Door usable height	800 mm
Number of drawers	0
Usable width	550 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer runner extension (partial/full extension)	100 %
Door opening angle	180 degrees
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Workbench casing

Accessories

Slide handle for GridLine Type KO12	914226 KO12
Shelf carriers for shelves of workbenches Type 12	927094 12
Pull-out shelf Type 1	927810 1
Fixed shelf, galvanized Type 1	927815 1