



OZ collet chuck, SK 40, Clamping range: 2-25mm



Order data

Order number	302475 2-25
GTIN	4062406110581
Item class	32A

Description

Version:

Ball-bearing power-clamping nut.

Application:

For clamping tools with plain shank in OZ collets to ISO 10897.

Optional extras:

OZ collets No. 309540 – 309560, Set No. 309562 (type 462 E) for size 2 – 25, C wrench No. 628400.

Technical description

Spare clamping nut No. 309670	2 - 25
External \varnothing D	60 mm
Suitable C-hook (pin) spanner No. 628400	58/62
Thread M	M16
Overhang dimension A	70 mm
Overall length L	163 mm
Clamping \varnothing D ₁	1-16 mm
Adapter	SK 40
Arbor standard	DIN 2080

Concentricity	≤ 3 μm
Type of product	Collet chuck