

**Side lock arbors, SK 50, Clamping range \varnothing D1: 10mm****Order data**

Order number	302435 10
GTIN	4062406110529
Item class	32A

Description**Version:**

Internal thread for manual clamping.

Application:

For clamping tools with side flat to DIN 1835 B and DIN 6535 HB.

Technical description

Overall length L	190 mm
Spare clamping screw No. 30 9900	10
External \varnothing D	35 mm
Thread M	M24
Overhang dimension A	63 mm
Clamping \varnothing D ₁	10 mm
Adapter	SK 50
Standard	DIN 6359
Arbor standard	DIN 2080
Concentricity	$\leq 3 \mu\text{m}$
Type of product	Side lock arbor

Accessories

Spare clamping screw for chucks with clamping \varnothing D1 10 mm

309900 10