

**Side lock arbors, SK 40, Clamping range \varnothing D1: 12mm****Order data**

Order number	302425 12
GTIN	4062406110079
Item class	32A

Description**Version:**

Internal thread for manual clamping.

Application:

For clamping tools with side flat to DIN 1835 B and DIN 6535 HB.

Technical description

External \varnothing D	42 mm
Thread M	M16
Overall length L	143 mm
Spare clamping screw No. 30 9900	12
Clamping \varnothing D ₁	12 mm
Overhang dimension A	50 mm
Adapter	SK 40
Standard	DIN 6359
Arbor standard	DIN 2080
Concentricity	$\leq 3 \mu\text{m}$
Type of product	Side lock arbor

Accessories

Spare clamping screw for chucks with clamping \varnothing D1 12 mm

309900 12