



## ER collet chuck, SK 40, for ER collet size: 40



### Order data

Order number	302485 40
GTIN	4062406110628
Item class	32A

### Description

#### Application:

For clamping tools with plain shank in ER / ESX collets to ISO 15488-B.

#### Optional extras:

ER collets No. 308981 – 309040, ER sets No. 309024 – 309320, ER clamping wrenches No. 309680 – 309740.

Concentricity:  $\leq 3 \mu\text{m}$

Clamping range: 4 - 26 mm

Overhang dimension A: 80 mm

External  $\varnothing$  D: 63 mm

Thread M: M16

Spare ER clamping nut: 40

### Technical description

External $\varnothing$ D	63 mm
Thread M	M16
Overhang dimension A	80 mm
Spare ER clamping nut	40
Clamping range	4 - 26 mm
Adapter	SK 40
Arbor standard	DIN 2080

Concentricity	≤ 3 μm
Type of product	Collet chuck