

**Side lock arbors, SK 50, Clamping range  $\varnothing$  D1: 16mm****Order data**

Order number	302435 16
GTIN	4062406110543
Item class	32A

**Description****Version:**

Internal thread for manual clamping.

**Application:**

For clamping tools with side flat to DIN 1835 B and DIN 6535 HB.

**Technical description**

Spare clamping screw No. 30 9900	16
Overall length L	190 mm
Clamping $\varnothing$ D <sub>1</sub>	16 mm
Overhang dimension A	63 mm
Thread M	M24
External $\varnothing$ D	48 mm
Adapter	SK 50
Standard	DIN 6359
Arbor standard	DIN 2080
Concentricity	$\leq 3 \mu\text{m}$
Type of product	Side lock arbor

---

## Accessories

Spare clamping screw for chucks with clamping  $\varnothing$  D1 16  
mm

---

309900 16