

**Side lock arbors, SK 50, Clamping range \varnothing D1: 20mm****Order data**

Order number	302435 20
GTIN	4062406110550
Item class	32A

Description**Version:**

Internal thread for manual clamping.

Application:

For clamping tools with side flat to DIN 1835 B and DIN 6535 HB.

Technical description

Clamping \varnothing D ₁	20 mm
Overhang dimension A	63 mm
Thread M	M24
Spare clamping screw No. 30 9900	20
Overall length L	190 mm
External \varnothing D	52 mm
Adapter	SK 50
Standard	DIN 6359
Arbor standard	DIN 2080
Concentricity	$\leq 3 \mu\text{m}$
Type of product	Side lock arbor

Accessories

Spare clamping screw for chucks with clamping \varnothing D1 20 mm

309900 20