



Side lock arbors, SK 40, Clamping range \varnothing D1: 16mm



Order data

Order number	302425 16
GTIN	4062406110086
Item class	32A

Description

Version:

Internal thread for manual clamping.

Application:

For clamping tools with side flat to DIN 1835 B and DIN 6535 HB.

Technical description

Clamping \varnothing D ₁	16 mm
Overhang dimension A	63 mm
Overall length L	156 mm
Thread M	M16
External \varnothing D	48 mm
Spare clamping screw No. 30 9900	16
Adapter	SK 40
Standard	DIN 6359
Arbor standard	DIN 2080
Concentricity	$\leq 3 \mu\text{m}$
Type of product	Side lock arbor

Accessories

Spare clamping screw for chucks with clamping \varnothing D1 16
mm

309900 16