

**Side lock arbors, SK 40, Clamping range  $\varnothing$  D1: 8mm****Order data**

Order number	302425 8
GTIN	4062406110055
Item class	32A

**Description****Version:**

Internal thread for manual clamping.

**Application:**

For clamping tools with side flat to DIN 1835 B and DIN 6535 HB.

**Technical description**

External $\varnothing$ D	28 mm
Thread M	M16
Spare clamping screw No. 30 9900	8
Overhang dimension A	50 mm
Clamping $\varnothing$ D <sub>1</sub>	8 mm
Overall length L	143 mm
Adapter	SK 40
Standard	DIN 6359
Arbor standard	DIN 2080
Concentricity	$\leq 3 \mu\text{m}$
Type of product	Side lock arbor

---

## Accessories

Spare clamping screw for chucks with clamping  $\varnothing$  D1 8  
mm

---

309900 8