



ER collet chuck, SK 40, for ER collet size: 25



Order data

| | |
|--------------|---------------|
| Order number | 302485 25 |
| GTIN | 4062406110604 |
| Item class | 32A |

Description

Application:

For clamping tools with plain shank in ER / ESX collets to ISO 15488-B.

Optional extras:

ER collets No. 308981 – 309040, ER sets No. 309024 – 309320, ER clamping wrenches No. 309680 – 309740.

Concentricity: $\leq 3 \mu\text{m}$

Clamping range: 1 - 16 mm

Overhang dimension A: 50 mm

External \varnothing D: 42 mm

Thread M: M16

Spare ER clamping nut: 25

Technical description

| | |
|---------------------------------------|-----------|
| Clamping range | 1 - 16 mm |
| External \varnothing D | 42 mm |
| Overhang dimension A | 50 mm |
| Spare ER clamping nut | 25 |
| Thread M | M16 |
| Clamping \varnothing D ₁ | 1-16 mm |
| Adapter | SK 40 |

| | |
|-----------------|----------------------|
| Arbor standard | DIN 2080 |
| Concentricity | $\leq 3 \mu\text{m}$ |
| Type of product | Collet chuck |