



ER collet chuck, SK 40, for ER collet size: 32



Order data

Order number	302485 32
GTIN	4062406110611
Item class	32A

Description

Application:

For clamping tools with plain shank in ER / ESX collets to ISO 15488-B.

Optional extras:

ER collets No. 308981 – 309040, ER sets No. 309024 – 309320, ER clamping wrenches No. 309680 – 309740.

Concentricity: $\leq 3 \mu\text{m}$

Clamping range: 2 - 20 mm

Overhang dimension A: 60 mm

External \varnothing D: 50 mm

Thread M: M16

Spare ER clamping nut: 32

Technical description

Overhang dimension A	60 mm
External \varnothing D	50 mm
Clamping range	2 - 20 mm
Spare ER clamping nut	32
Thread M	M16
Clamping \varnothing D ₁	2-20 mm
Adapter	SK 40

Arbor standard	DIN 2080
Concentricity	$\leq 3 \mu\text{m}$
Type of product	Collet chuck