

**Side lock arbors, SK 50, Clamping range \varnothing D1: 25mm****Order data**

Order number	302435 25
GTIN	4062406110567
Item class	32A

Description**Version:**

Internal thread for manual clamping.

Application:

For clamping tools with side flat to DIN 1835 B and DIN 6535 HB.

Technical description

Thread M	M24
Overall length L	207 mm
Spare clamping screw No. 30 9900	25
External \varnothing D	65 mm
Clamping \varnothing D ₁	25 mm
Overhang dimension A	80 mm
Adapter	SK 50
Standard	DIN 6359
Arbor standard	DIN 2080
Concentricity	$\leq 3 \mu\text{m}$
Type of product	Side lock arbor

Accessories

Spare clamping screw for chucks with clamping \varnothing D1 25
mm

309900 25