

Garant
Shrink-fit chuck 3°, BT 40 A = 90, Clamping range Ø D1: 6mm

Order data

Order number	303443 6
GTIN	4062406110666
Item class	31A

Description
Version:

- All shanks hard turned.
- Extra slim design (3° contour).

Application:

- Especially for tool and mould making.
- Wherever reduced interference contours are required.
- For clamping tools with shank tolerance h6.

Optional extras:

Pull studs (PS) No. 308760 – 308806, shrink-fit chuck extensions No. 302410, sizes 12/3 and 12/4, shrink-fit units No. 354210 – 304450, PS wrenches No. 308820 – 308835.

Note:

No length adjustment available!

Technical description

Clamping Ø D ₁	6 mm
Overhang dimension A	90 mm
Ø D ₂	12 mm
External Ø D	19 mm
Adapter	BT 40 A = 90
Arbor standard	ISO 7388-2

Arbor standard	JIS B6339
Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HSC
Machining strategy	HPC
Type of product	Shrink-fit chuck

Accessories

Wrench for pull studs ISO 7388 suitable for ISO taper size 40	308830 40
Pull stud 45° sealed suitable for steep tapers 40	308760 40
Wrench for pull studs DIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
Pull stud 60° sealed suitable for steep tapers 40	308785 40
Pull stud Hurco 90° with fit sealed suitable for steep tapers 40	308806 40
Pull stud 90° sealed suitable for steep tapers 40	308795 40
Pull stud 45° sealed suitable for steep tapers 40	308765 40
Pull stud 90° sealed suitable for steep tapers 40	308790 40
Hurco 45° pull stud with 4-mm bore and fit sealed suitable for steep tapers 40	308801 40
Pull stud Hurco 45° with fit sealed suitable for steep tapers 40	308802 40