



## Combination face mill adapter, SK 50 A = 55, Spigot Ø d1: 40mm



### Order data

Order number	302515 40
GTIN	4062406111120
Item class	32A

### Description

#### Version:

Internal thread for manual clamping.

#### Application:

**With drive key** for milling cutters **with longitudinal groove**, e.g. DIN 841.

**With face mill drive ring** for milling cutters with **transverse slots**, DIN 1880.

#### Supplied with:

Drive key, face mill drive ring, and lock screw.

#### Optional extras:

Special toggle spanner No. 309840.

### Technical description

Overall length L	209 mm
Spare drive ring No. 309870	40
Overhang dimension A	55 mm
Milling mandrel length L <sub>3</sub> with drive ring	27 mm
Suitable toggle spanner No. 309840	40
Milling mandrel length L <sub>4</sub>	41 mm
Thread M	M24
Spare milling cutter lock screw No. 309860 / 309861	40

Clamping $\varnothing D_1$	40 mm
Adapter	SK 50 A = 55
Standard	DIN 6358
Arbor standard	DIN 2080
Concentricity	$\leq 6 \mu\text{m}$
Type of product	Milling cutter spigot