

Garant GRIDLINE

**16G cabinet casing for individual configuration with drawers, 12×20G,
Height: 400mm****Order data**

Order number	927412 400
GTIN	4062406111229
Item class	9GG

Description**Version:**

16G cabinet casing for individual configuration with drawers, in sturdy steel construction. Can be locked centrally with a cylinder lock.

Colour:

Light grey RAL 7035, **powder-coated**.

Note:

When equipping the cabinet with drawers, check that the sum of the individual drawer front heights adds up to the usable cabinet height.

Sizes 600 and 700 suitable only for Ready-to-go workbenches.

Technical description

Width	400 mm
Number of drawers	0
Depth	650 mm
Usable height for drawers	325 mm

Weight	11.5 kg
Usable height	325 mm
Number of doors	0
Usable width	350 mm
Height	400 mm
Version	for individual configuration
Number of pull-out shelves	0
Material thickness	1 mm
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	12x20G
Type of product	Workbench casing

Accessories

Lock plate for GridLine Type KO21	914227 KO21
-----------------------------------	-------------