

Garant GRIDLINE

Storage shelf, Front height: 100mm**Order data**

Order number	935140 100
GTIN	4062406111434
Item class	9GK

Description**Version:**

Made of sheet metal with cross-bracing on the underside. Always required when it is intended to combine swing doors / sliding doors with drawers. This is necessary because the swing doors / sliding doors require stops 50 mm above and below them as part of the front fittings. **Load capacity 200 kg.**

Colour:

Light grey RAL 7035, **powder-coated.**

Note:

- **The storage shelf also acts as the locking base in combination with the central locking No. 935590, 935595. Prepared for mounting cylinder locks in the fascia.**
- **25 mm high storage shelves cannot be combined with intermediate bridging rails and end rails.**

Technical description

Front height	100 mm
Storage shelf version	straight shelf
Storage shelf version	slotted shelf
Shelf load capacity / maximum distributed shelf load (on metal)	200 kg
Application range	Drawer/shelf combination unit
Material thickness	1.2 mm

Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Width	953 mm
Depth	675 mm
Width in G	36
Depth in G	24
Type of product	Storage shelf