

Garant GRIDLINE**Open 24G casing with recessed base, Height: 700mm****Order data**

Order number	927700 700
GTIN	4062406111519
Item class	9GG

Description**Version:**

Open 24G casing with sturdy sheet metal construction.
With recessed base and shelf, (powder-coated, RAL 7035 light grey).

Suitable for:

Can be incorporated only into a Ready-to-go workbench. Not suitable for Vario workbenches.

Fitted with:

Number of height-adjustable storage shelves: 1

Colour:

Body RAL 7035 light grey, **powder-coated**.

Technical description

Depth	650 mm
Width	600 mm
Weight	17 kg
Height	700 mm
Material thickness	1 mm

Height adjustment interval	25 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Workbench casing