

Garant GRIDLINE

Open 24G casing with full depth base, Height: 700mm**Order data**

Order number	927705 700
GTIN	4062406111557
Item class	9GG

Description**Version:**

Open 24G casing with sturdy sheet metal construction.

With full depth base and shelf, (galvanised).

Suitable for:

Can be incorporated into all workbenches.

Fitted with:

Number of height-adjustable storage shelves: 1

Colour:

Body RAL 7035 light grey, **powder-coated.**

Technical description

Height	700 mm
Depth	650 mm
Width	600 mm
Weight	22.8 kg
Material thickness	1 mm

Height adjustment interval	25 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Workbench casing

Accessories

Fixed shelf, galvanized Type 1	927815 1
Shelf carriers for shelves of workbenches Type 12	927094 12
Pull-out shelf Type 1	927810 1