

Garant GRIDLINE

**Sliding doors set, Drawer width 2×26G, Height including frame: 1000mm****Order data**

Order number	935630 1000
GTIN	4062406111502
Item class	9GK

**Description****Version:**

The doors are reinforced on the inside and run on ball bearing guides in rails. Lockable by slide handle with a **cylinder lock**. The front fittings kit consists of 2 side stops, 2 guide rails, and 2 door leaves. The shelf bays behind the sliding doors can be fitted with storage shelves, drawers, and pull-out shelves (exception: behind sliding doors No. 935640 only storage shelves can be fitted, no drawers or pull-out shelves).

**Colour:**

Frame RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

**Technical description**

Usable height	900 mm
Height including frame	1000 mm
Frame depth	80 mm
Application range	Drawer/shelf combination unit
Material thickness	1.2 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Product name attribute	Drawer width 2x26G
Type of product	Sliding door