

Garant GRIDLINE

24G casing for individual configuration with drawers, 20×20G, Height: 300mm**Order data**

Order number	927720 300
GTIN	4062406111656
Item class	9GG

Description**Version:**

24G casing for individual configuration with drawers in sturdy steel construction. Can be locked centrally with cylinder lock.

Colour:

Light grey RAL 7035, **powder-coated**.

Note:

When equipping the cabinet with drawers, check that the sum of the individual drawer front heights adds up to the usable cabinet height.

Size 600 and 700 only suitable for Ready-to-go workbenches.

Technical description

Usable height for drawers	225 mm
Depth	650 mm
Weight	11.6 kg
Usable height	225 mm
Width	600 mm
Number of drawers	0
Usable width	550 mm

Number of doors	0
Height	300 mm
Version	for individual configuration
Number of pull-out shelves	0
Material thickness	1 mm
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x20G
Type of product	Workbench casing