

Garant GRIDLINE

**24G casing for individual configuration with drawers, 20×20G, Height: 700mm****Order data**

Order number	927720 700
GTIN	4062406111694
Item class	9GG

**Description****Version:**

24G casing for individual configuration with drawers in sturdy steel construction. Can be locked centrally with cylinder lock.

**Colour:**

Light grey RAL 7035, **powder-coated**.

**Note:**

When equipping the cabinet with drawers, check that the sum of the individual drawer front heights adds up to the usable cabinet height.

Size 600 and 700 only suitable for Ready-to-go workbenches.

**Technical description**

Usable height for drawers	625 mm
Width	600 mm
Number of drawers	0
Depth	650 mm

Weight	19.6 kg
Usable height	625 mm
Number of doors	0
Usable width	550 mm
Height	700 mm
Version	for individual configuration
Number of pull-out shelves	0
Material thickness	1 mm
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x20G
Type of product	Workbench casing