

Garant GRIDLINE

**Casing 24G with door hinged on the right, for individual configuration with drawers, 20×20G, Height / door height: 800/525mm****Order data**

Order number	927725 800/525
GTIN	4062406111731
Item class	9GG

**Description****Version:**

24G casing with cupboard, for individual configuration with drawers in sturdy steel construction. Can be locked centrally with cylinder lock. Door hinged on the right.

**Fitted with:**

Number of height-adjustable storage shelves: 1

**Colour:**

Body RAL 7035 light grey, door RAL 7016 anthracite **powder-coated**.

**Note:**

When equipping the cabinet with drawers, check that the sum of the individual drawer front heights adds up to the usable cabinet height.

Sizes 600/425 and 700/525 suitable only for Ready-to-go workbenches.

**Technical description**

Width	600 mm
Door stop	right-hand

Number of height-adjustable shelves	1
Height	800 mm
Usable width	550 mm
Depth	650 mm
Door usable height	525 mm
Weight	33.3 kg
Usable height for drawers	150 mm
Version	for individual configuration
Material thickness	1 mm
Door opening angle	180 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	Workbench casing

## Accessories

Slide handle for GridLine Type KO12	914226 KO12
Drawer Drawer front height 50 mm	927800 50
Fixed shelf, galvanized Type 1	927815 1
Drawer Drawer front height 100 mm	927800 100
Drawer Drawer front height 75 mm	927800 75
One-hand individual drawer release system Drawer usable width in G 20	951020 20
Pull-out shelf Type 1	927810 1
Shelf carriers for shelves of workbenches Type 12	927094 12